



### Standards

EN140: 1998 Mask Body  
EN143: 2000+A1: 2006 P3 RD  
CE 0194

### Efficiency

P3 >99,95% for 0,3 µ particulate

### Shelf Live


5 years (mask & filters) See storage conditions on Instructions for Use.  
Filters are re-usable and changeable.

### Material




- **Mask:** Medical grade TPE Conforms to ISO 10993-10: 2010 for irritations. Mask body latex and silicone free, odour free. Valve Body in Nylon, Inhalation/Exhalation diaphragm in Silicone. 4 point adjustable elasticated head and neck strap with comfort pad in TPE.
- **Filters:** Mechanical type multi-layer HESPA Synthetic media with TPE flexible overmolded / encapsulated.

### Production

United Kingdom  
100% of filters NaCl Tested



**Encapsulation (patented technology)**  
645 mm; length of actual media in each filter

Code	Description	Quantity
 SPR299 (S/M) SPR501 (M/L)	Elipse Half Mask complete with P3 filters	10 pcs. per box
 SPR316	Elipse P3 replacement filters	10 sets of 2 pcs. per box
 SPM001	Elipse Dust Mask Carry Case (Belt holder)	10 sets per box
 SPM414	Portacount Face Fit Kit adaptor	10 sets per box

## Applications - dust, mist and fumes

### Welding and Grinding

Metal Fumes and Dust



### Construction

Silica Dust, Abestos, Concrete Dust, Stone Dust, Aggregate Dust, Wood Dust, Cement Dust, Mold



### Mining

Coal Dust, Silica Dust



### Manufacturing

Glass Fibres, Composite Fibres, Lead Fumes



### Food

Poultry, Powders (Dairy), Spices, Grain Dust



### Pharmaceutical

Powders, Viruses

