

# SPRINGFIT™ 400 SERIES

PRODUCT CODE: BGA\_\_2-20\_-\_00

**TECHNICAL  
SPECIFICATION**

**RESPIRATORY PROTECTION**

## INSTRUCTIONS FOR USE

Mask must be fitted in accordance with the instructions supplied

Care must be taken to ensure that the correct mask type is selected for the work to be carried out

If in doubt as to the type of mask required seek professional guidance

## PERFORMANCE

Springfit™ 421 and 425 offer an assigned protection factor (APF) of 10 x Workplace Exposure Limit (WEL) for fine non-toxic dusts, fibres and mists

Springfit™ 431, 435 and 436 offer an APF of 20 x WEL for fine non-toxic dusts, fibres and mists

Respiratory protection is only effective if it is correctly selected, fitted and worn throughout the time when the wearer is exposed to respiratory contaminants

## SPRINGFIT™ OPTIONS

Springfit™ Model	EN 149 Classification	Typhoon™ Valve	Carbon Filter
421	FFP2 NR D	No	No
425	FFP2 NR D	Yes	No
431	FFP3 NR D	No	No
435	FFP3 NR D	Yes	No
436	FFP3 NR D	Yes	Yes

## CLEANING & MAINTENANCE

Not applicable - disposable product

Store the masks out of sunlight away from chemicals in a dry atmosphere

### MAN MADE FIBRES:

The mask has an ergonomic 3D design to fit most face shapes



### POLYPROYLENE INNER SKELETON:

Ensures good seal by absorbing facial movements



## SPRINGFIT™ FEATURES

**Face Seal:** Improved face seal for added comfort

**Typhoon™ Valve:** Optional Modern design valve allows for lower breathing resistance

**Carbon Filter:** The Springfit™ 436 has an integrated Carbon filter to help reduce nuisance odours

## CONFORMITY & MARKINGS

Meets the FFP2 and FFP3 requirements of EN149 (as applicable)

EC Certificate Number 560229, issued by BSi Product Certification

EN149:2001 + A1:2009

**PRODUCT CODE: BGA 2-20 - 00**

## RESPIRATORY PROTECTION

Box Quantity: 10



Box Quantity: 10



Box Quantity: 100



Box Quantity: 100



## DIMENSIONS OF SPRINGFIT™ 421, 431

Depth: 60mm

Width: 210mm

Height: 125mm

Weight: 13.5g (Approx)

## DIMENSIONS OF SPRINGFIT™ 425, 435, 436

Depth: 70mm

Width: 210mm

Height: 125mm

Weight: 18.8g (Approx)

## LIMITATIONS OF USE

Protection will only be offered if the mask is fitted correctly

The mask, when in contact with the skin may cause allergic reactions to susceptible individuals

If this occurs leave the hazard area, remove mask and seek medical advice

The use by date is printed on the outer packaging

Do not use where exposure to chemical gases may be experienced

Use in well ventilated areas only, which are not deficient in oxygen and do not contain explosive atmospheres

Ensure good seal around the face is created before entering the hazard area

The working life of the mask is nominally one day (this is based on an working day shift of 8 hours), however it may be affected by many factors, including work rate, airflow and concentration of any contaminant in the atmosphere. The mask should be changed immediately if,

- a.) Breathing difficulties due to clogging are experienced,
- b.) Breakthrough of a contaminant is detected by smell, taste or any other means, or
- c.) The mask becomes damaged

This mask is not designed to be worn by people with facial hair