

## EVO100 Pulsar® Evolution Storm Coat

- 3 layer, 100% polyester woven twill with highly breathable PU laminate membrane.
- Original Pulsar® chevron design thermally applied 3M™ Scotchlite™ Reflective Tape to body & sleeves with segmented comfort trim shoulder braces.
- Reflective blue piping and chevron detail for increased night time visibility and improved modern appearance.
- Full length YKK® 2-way interactive zip fastening.
- Double storm flap system concealing a zipped pocket and pen sleeves.
- Full width lower document pockets with self-closing flaps.
- Side hand warmer pockets with zip fastening.
- Velcro adjustable wrap around storm cuffs.
- Neoprene inner cuff for increased comfort.
- Hidden zipped chest pocket to right hand breast as worn.
- Underarm ventilation.
- Internal breast pocket.
- Unique flip out ID window.
- Chin protector.
- 100% polyester mesh lining for enhanced breathability.
- Draw cord in body.
- Two internal A4 sized poachers pockets.
- Interacts with Pulsar/Pulsarail Bodywarmers (P422/PR498), Fleece Jackets (P507/PR508) and Soft Shell Jackets (P534/PR535).

## EVO102 Pulsar® Evolution Arctic Hood

- 3 layer, 100% polyester woven twill with highly breathable PU laminate membrane.
- Original Pulsar® thermally applied reflective blue chevron detail for increased night time visibility.
- Face and crown adjustment for optimal fit.




	Coat	Hood
<b>Code:</b>	EVO100	EVO102
<b>Sizes:</b>	XS - 6XL	One Size
<b>Colour:</b>	Yellow	Yellow
<b>Standards:</b>	EN ISO 20471:2013 Class 3 EN343:2003 Class 3:3	

### Quick Size Guide (To fit chest)

XS 31" - 34"	3XL 50" - 55"
S 34" - 37"	4XL 55" - 59"
M 37" - 40"	5XL 59" - 63"
L 40" - 43"	6XL 63" - 66"
XL 43" - 46"	7XL 66" - 70"
2XL 46" - 50"	

Please note: out sizes may be available through special production runs.

### Branding Guide



Measurements are based on a size small garment. This should be used as a guide only and before applying any logo you should check to ensure it fits correctly and does not encroach on to the retro reflective bands.

Incorporating



Aftercare



Maximum x 25 wash cycles.  
Do not wash in biological powder, wash as synthetics.  
40° domestic wash only, hang dry, do not iron.  
Do not tumble dry, do not dry clean, do not use bleach.  
Do not use fabric softener.